

10,0000m²

Company Profile And Culture

JAMAL , INC. is a professional intelligent toilet manufacturer intearating product development, desian, production and sales.

The head office has multiple factories, branches and offices, covering a total area of 150 mu ,with a standardized workshop area of 100000 saquare meters, and currently employs more than 700 people.

The company advocates people-oriented, pragmatic, innovative, professional, and enterprising philosophy, focusing on the inteligent bathroom field, relying on high-quality research and development teams, high-end research and development laboratories, and focusing on product differentiation research and development, The company has successively passed ISO9001,CE,CQC and other product and enterprise management certifications, adherina to the spirit of diligence and dedication.and striving to create a first-class intelligent bathroom brand in China




JAMAL , INC.

OFFICE ADD:NO.218-26 WANGSHAN ROAD,JINGBEI DIST,NINGBO,CHINA 315000
FACTORY ADD:NO.555 BINHAI ROAD,FENGHUA DIST,NINGBO,CHINA 315000
TEL:+86-574-87151980 FAX:+86-574-87151980
EMAIL:info@jamal.cn WEB:www.jamal.cn



Company Development History



Unlock New Technology Enjoy New Experiences

01 | UV Sterilization Avoid Cross Infection

Strong inner wall sterilization, Rapidly destroy bacteria and viruses, Automatic disinfection of spray bar retraction, After cleaning then 10 seconds from the seat, the nozzle will be automatically turned on for 600 seconds for ultraviolet sterilization. Sterilization rate up to 99%.

广微测
Gmicro Testing

广东省微生物分析检测中心
GUANGDONG DETECTION CENTER OF MICROBIOLOGY

分析检测报告
REPORT FOR ANALYSIS

报告编号
Report No. 2021SP07761101D

样品名称
Name of Sample 马桶喷嘴杀菌
Sterilize toilet nozzle

委托单位
Applicant 宁波芬尼卫浴有限公司
Ningbo Finio Sanitary Ware Co., Ltd.

检测类型
Test Type 委托检测
Entrusted Test

单位地址
Address 广州市先烈中路 500 号大院 64 号楼
Building 64, No.500, Xianle Middle Road, Guangzhou, C. China

邮编
Postcode 510670

电话
Tel (020)87137666

传真
Fax (020)87137668

网址
Website www.gdmicro.com

广东省微生物分析检测中心
GUANGDONG DETECTION CENTER OF MICROBIOLOGY

分析检测报告
REPORT FOR ANALYSIS

报告编号 (Report No.): 2021SP07761101D 验证编号 (Verification Code): 2084738

样品名称 Name of Sample	委托检测 Entrusted Test
马桶喷嘴杀菌 Sterilize toilet nozzle	委托检测 Entrusted Test
样品名称 Sample Name	样品名称 Sample Name
样品规格和型号 Type and Lot No. of Sample	样品规格和型号 Type and Lot No. of Sample
检测日期 Date	检测日期 Date
检测标准和方法 Test Standard and Method	检测标准和方法 Test Standard and Method
检测结果 Test Result	检测结果 Test Result

检测结论
Test Conclusion

报告日期
Report Date

报告编号
Report No.

报告日期
Report Date

02 | Electrolytic water Sterilization Healthy Cleaning

Adopt electrolytic water sterilization technology to effectively remove bacteria and dirt. Avoid cross infection and take care of family health. The electrolytic water produced by the electrolytic water device has a high killing rate against Escherichia coli and Staphylococcus aureus.

广微测
Gmicro Testing

广东省微生物分析检测中心
GUANGDONG DETECTION CENTER OF MICROBIOLOGY

分析检测报告
REPORT FOR ANALYSIS

报告编号
Report No. 2021FM121801D

样品名称
Name of Sample 电解水模块
Electrolytic water module

委托单位
Applicant 宁波芬尼卫浴有限公司
Ningbo Finio Sanitary Ware Co., Ltd.

检测类型
Test Type 委托检测
Entrusted Test

单位地址
Address 广州市先烈中路 100 号大院 64 号楼
Building 64, No.100, Xianle Middle Road, Guangzhou, C. China

邮编
Postcode 510670

电话
Tel (020)87137666

传真
Fax (020)87137668

网址
Website www.gdmicro.com

广东省微生物分析检测中心
GUANGDONG DETECTION CENTER OF MICROBIOLOGY

分析检测报告
REPORT FOR ANALYSIS

报告编号 (Report No.): 2021FM121801D 验证编号 (Verification Code): 8332087


样品名称 Name of Sample	委托检测 Entrusted Test
电解水模块 Electrolytic water module	委托检测 Entrusted Test
样品名称 Sample Name	样品名称 Sample Name
样品规格和型号 Type and Lot No. of Sample	样品规格和型号 Type and Lot No. of Sample
检测日期 Date	检测日期 Date
检测标准和方法 Test Standard and Method	检测标准和方法 Test Standard and Method
检测结果 Test Result	检测结果 Test Result

检测结论
Test Conclusion

报告日期
Report Date

报告编号
Report No.

报告日期
Report Date



03 | Foam Shield: Splash Proof, No Odor

Equipped with unique foam shield technology, Form a dense foam layer on the toilet,
Effectively avoid splashing, sticky, peculiar smell, bacteria and other problems, More humanized solution to the problem of domestic toilet, bringing a super toilet experience.



04 | Partial Function Display

One Button Knob
Simplify and Easy Operation



Water Purification Technology
Durable Antifouling And Easier To Clean



Hydrodynamic Flushing System
Strong and Carefree Momentum



Induction Flap
Touch Free Opening



Intelligent Sensing Instant Flushing
Sit or Stand Automatic Flushing



High Frequency Pulse Massage
Clean and Comfortable



Cleaning Intelligent Positioning
Accurate Cleaning



Everlasting Clean Sterilization 2.0
360° Sterilization and Bacteriostasis



Company's Comprehensive Strength

Intimate Service

Sanhe Intelligent Sanitary Ware has focused on the sanitary ware industry for 15 years, and has established a comprehensive and complete service system. The 400 call center team responds to customer hotline inquiries 7 * 24 hours, and provides door-to-door service within 72 hours, creating a new consumer experience for consumers. It provides high-quality services from pre sales, during sales, and after sales to serve customers wholeheartedly.

Production Strength

Our company quotes advanced technology and production equipment from Europe and the United States, and through independent innovation, has developed a series of fashionable, energy-saving, and high-quality intelligent toilets. The main components of the products are imported from Japan, Italy, and other countries, with performance reaching the same level abroad.

Comprehensive Strength

Test Equipment

Our company has complete, reliable, and advanced testing equipment to test and inspect the appearance, performance, safety, and other aspects of all products to ensure that the products meet various quality standards.

Technical Quality

Sanhe Intelligent Sanitary Ware has always focused on introducing professional talents and advanced equipment. Currently, there are multiple senior professionals in the automation structure, software design, and electronic engineering industries, as well as multiple assembly lines used for product production and assembly, and laboratories that meet national testing standards have been established to comprehensively test the performance of products to ensure that products fully comply with industry and national quality standards.



Test Equipment

NO.1 Damping Buffer Durability Testing Machine

According to Article 5.4.6 of JC/T 764-2008, it still meets the performance requirements after 30000 tests.

Internal control of our company:
Taking 60000 times as a cycle, the product still meets the performance requirements after a total of 300000 or more consecutive 5 cycles.



NO.2 Left And Right Swing Durability Testing Machine

According to Article 5.4.2 of JC/T 764-2008, it still meets the performance requirements after 25000 tests.

Internal control of our company:
Taking 60000 times as a cycle, the product still meets the performance requirements after a total of 180000 or more consecutive 3 cycles.



NO.3 Gravity Impact Testing Machine

According to Article 9.4.55 of T/CBMF 15-2019, it still meets the performance requirements after 20000 tests.

Internal control of our company:
It still meets the performance requirements after 100000 consecutive times or more.



NO.4 Intelligent Toilet Energy And Water Efficiency Comprehensive Testing Machine

According to GB 38448-2019, the limited values and grade standards for energy efficiency and water efficiency of intelligent toilets.

Test the water consumption for product flushing and cleaning functions, the water consumption for flushing, and the power consumption and power consumption of the entire machine.



NO.5 Rain Testing Machine

According to Article 9.4.6 of CBMF-15-2016, complete machine life test: at least 25000 times, whether there are any components or abnormal functions.

Test the durability of bathing, and the safety regulations, functions, and product performance still meet the requirements.



NO.6 Base Comprehensive Test

According to the limit requirements for product rated power in GB4706.1.

After testing, the product must meet the functional and rated power limit requirements.

